SATCO' NUVO

Project Name

Location

Prepared By



SATCO S11851

15WLED/CDL/6/CCT/120-277

Notes

General Status Active Recessed Can Size 6 in. 15W Wattage Voltage 120V-277V Finish White 2700K/3000K/3500K/4000K/5000K CCT (Kelvin) Color Temperature Warm to Cool White Lumen Output 1600L Indoor or Outdoor Fixture Indoor and Outdoor Specifications LED Technology CRI 80 Beam Angle 90 Rated Hours 50000 **Operating Temperature** -20C (-4F) to +40C (+104F) Dimmable Yes-Dimmable **Dimming Note** 0-10V Dimming Only Sloped Ceiling Yes Dimensions Width (in.) 7.40 Height (in.) 3.46 Weight (lb.) 1.05 Compliance cETLus - Listed Safety Listing Location Rating Wet Energy Star Yes ES Unique ID ESID-2401357 IC Rated Yes T20 Exempt - Fixtures Not CA T20 / T24 Rationale Regulated California Status Lawful for sale in California Title 20 / 24 Status Lawful for sale California Prop 65 Lead **RoHS** Compliant Yes FCC Compliant Yes SDS Sheet LED_Fixture

Additional Information

Warranty

5 Year Limited - Fixtures

For More Information Visit: <u>http://www.satco.com/</u>

