

Project Name

Location

Prepared By



SATCO S11852

22WLED/CDL/8/CCT/120-277

Notes

[www] 10-24-2020 09:32:00

General

Status	Active
Recessed Can Size	8 in.
Wattage	22W
Voltage	120V-277V
Finish	White
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Color Temperature	Warm to Cool White
Lumen Output	2200L
Indoor or Outdoor Fixture	Indoor and Outdoor

Specifications

Technology	LED
CRI	80
Beam Angle	90
Rated Hours	50000
Operating Temperature	-20C (-4F) to +40C (+104F)
Dimmable	Yes-Dimmable
Dimming Note	0-10V Dimming Only
Sloped Ceiling	Yes

Dimensions

Width (in.)	9.76
Height (in.)	3.97
Weight (lb.)	1.41

Compliance

Safety Listing	cETLus - Listed
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2401358
IC Rated	Yes
CA T20 / T24 Rationale	T20 Exempt - Fixtures Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------