

Project Name

Location

Prepared By



## SATCO S11905

4W/LED/T5/840/BP

### Notes

[www] 10-11-2021 02:00:30

### General

Status	Active
Watts	4W
Fluorescent Equivalent	8W
Volts	120V-277V
Ballast Type	Type B
Shape	T5
Base	Miniature Bi Pin
ANSI Base	G5
Nominal Length	12
Finish	Frost
CCT (Kelvin)	4000
Temperature	Cool White
CRI	82
Lumens	400L
Beam Spread	240
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Linear
Technology	LED

### Electrical

Ballasting Requirements	No ballast or external driver required
Operating Frequency	50/60 Hz
Power Factor	0.9
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

### Physical

MOL	11.91
MOD	0.83
Material	Glass
Lens Finish	Frost
Weight (lb.)	0.08

### Additional Information

Additional Info	Replaces F8T5/CW lamps
Shatter-Proof Type	PET Coated
Installation Notes	Direct wire 120-277V line voltage; Double ended wiring
Warranty	5 Year Limited - T5 LED Bulbs - Ballast Bypass

### Compliance

Safety Listing	cULus Classified
Location Rating	Damp
Energy Star	No
California Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes

