

## 4 Inch Round Ceiling Box

S120JFAN



Ceiling Fan Box, Premium Grade with integral fan mounting bracket and four Auto/Clamps. 12 pack.



### features & benefits

- Constructed of impact-resistant Noryl thermoplastic, making it virtually unbreakable and non-conductive.
- Auto Clamp cable clamps molded in, hold wire securely in box.
- UL Listed for fan and fixture support.
- Large, 20.25 cubic inch capacity for extra wiring space.
- Depth-mounting gauge at bottom of bracket helps you align the box at the proper depth relative to the ceiling.
- Angled, rugged, metal mounting bracket safely and securely fastens fans or fixtures to the building structure.
- Dual mounting accepts fans or fixtures with 2.75 inch or 3.5 inch straps.
- Fan mounts directly to bracket through box with #10-32 screws (provided).
- Phillips-head screws (#10-32 x 3 inch) mount the fan or fixture directly to the metal bracket.
- Ringed nails for tighter grip.

### specifications

#### General Info

Size: 4"  
Type: Ceiling Box  
Special Features: Round

#### Listing Agencies/Third Party Information

CSA Listing Info: No  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: Yes  
UN SPS C: 39121308  
UR: No

**Dimensions**

Depth U S: 2.1875  
Diameter U S: 4  
Volume: 20.25

**Technical Information**

Material: Plastic  
Mounting: Auto Clamps  
Shape: round

**Buy American Act Compliance**

Country of Origin: UNITED-STATES-OF-AMERICA  
Buy American Act Status: Buy American Act Compliant