

Project Name

Location

Prepared By



SATCO S12400

5A15/CL/LED/E26/927/120V

Notes

[www] 10-11-2021 02:00:30

General

Status	Active
Watts	5W
Incandescent Equivalent	40W
Volts	120V
Shape	A15
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	2700
Temperature	Warm White
CRI	90
Lumens	450L
Beam Spread	320
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60 Hz
Candlepower	40
Dimming Type	Forward Phase or Reverse Phase or Phase Selectable
Power Factor	0.7
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	3.39
MOD	1.89
Weight (lb.)	0.05

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cULus Listed
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2384830
California Status	Lawful for sale
RoHS Compliant	Yes
SDS Sheet	LED_Lamp