



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S12415 8W 6.5A19 CL Led E26 30K 120V

Satco

Catalog Number	S12415
Manufacturer	Satco
Description	8 Watt Led A19 Lamp - Clear Medium Base 3000K 90 Cri 120 Volts
Weight per unit	0.1200 (lbs/each)
Product Category	Lighting

Features

average life	15000
Base	E26
beam angle	320
dimnable	Yes-Dimmable
lumens	800
Material	Glass; Aluminum
Power Factor	0.7
Shape	A19
Voltage Rating	120
Warranty	3 Year Limited
Wattage	8

Material, Color, and Finish

color rendering index (cri)	90+
color temperature	3000
Finish	Clear

Dimensions and Weight

Size	4.02
------	------

Descriptions

Description	8W 6.5A19 CL LED E26 30K 120V
extra long description	SATCO S12415 8A19/CL/LED/E26/930/12
Long Description	8 Watt LED A19 Lamp - Clear Medium Base 3000K 90 CRI 120 Volts
Product Type	8A19/CL/Led/E26/930/120V
Special Features	Warranty: 2-Years ; Location Rating: Wet ; Operating Temp: -20C (-4F) to +45C (+113F) ; Material: Aluminum / Glass ; Indoor Outdoor: Indoor;Outdoor ; Color Temp: Soft White ; Efficacy: 100.00 LPW ; Candle Power: 60 ; DLC Approved: False ; FCC Compliant: True ; Indoor Outdoor: Indoor;Outdoor ; Lamp Filament: LED Filament ; ANSI Base: E26 ; Amps: 0.067A



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Satco
GTIN	00045923124150
Manufacturers Part Number	S12415
UPC	045923124150

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
Type	LED General Service

Packaging

Carton	1
Weight	0.07
Weight Per each	0.12

Uses, Certifications, and Standards

Application	LED
Operating Temperature standard	-20C (-4F) to a maximum of +45C (+113F) cULus - Certified;cULus - Listed