

Project Name

Location

Prepared By



SATCO S12415

8A19/CL/LED/E26/930/120V

Notes

[www] 11-06-2021 02:55:02

General

Status	Active
Watts	8W
Incandescent Equivalent	60W
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	3000
Temperature	Soft White
CRI	90
Lumens	800L
Beam Spread	320
Dimmable	Yes-Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60 Hz
Candlepower	60
Dimming Type	Forward Phase or Reverse Phase or Phase Selectable
Power Factor	0.7
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	4.02
MOD	2.36
Weight (lb.)	0.07

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cULus Listed
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2386994
California Status	Lawful for sale
RoHS Compliant	Yes
SDS Sheet	LED_Lamp