



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S12419 8.2W 120V 90CRI 27K Led A19

Satco

Catalog Number	S12419
Manufacturer	Satco
Description	8.2 Watt Led A19 Lamp - Soft White Medium Base 2700K 90 Cri 120 Volts
Weight per unit	0.1200 (lbs/each)
Product Category	20210304095133

Features

average life	15000
Base	E26
beam angle	320
dimnable	Yes-Dimmable
lumens	800
Material	Glass; Aluminum
Power Factor	0.7
Shape	A19
Voltage Rating	120
Warranty	3 Year Limited
Wattage	8.2

Material, Color, and Finish

color rendering index (cri)	90+
color temperature	2700
Finish	Soft White

Dimensions and Weight

Size	4.02
------	------

Descriptions

Description	8.2W 120V 90CRI 27K LED A19
extra long description	SATCO S12419 8.2A19/SW/LED/E26/927/
Long Description	8.2 Watt LED A19 Lamp - Soft White Medium Base 2700K 90 CRI 120 Volts
Product Type	8.2A19/SW/Led/E26/927/120V
Special Features	Warranty: 2-Years ; Location Rating: Wet ; Operating Temp: -20C (-4F) to +45C (+113F) ; Material: Aluminum / Glass ; Indoor Outdoor: Indoor;Outdoor ; Color Temp: Warm White ; Efficacy: 97.56 LPW ; Candle Power: 60 ; DLC Approved: False ; FCC Compliant: True ; Indoor Outdoor: Indoor;Outdoor ; Lamp Filament: LED Filament ; ANSI Base: E26 ; Amps: 0.068A



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Satco
GTIN	00045923124198
Manufacturers Part Number	S12419
UPC	045923124198

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	LED General Service

Packaging

Carton	1
Weight	0.07
Weight Per each	0.12

Uses, Certifications, and Standards

Application	LED
Operating Temperature standard	-20C (-4F) to a maximum of +45C (+113F) cULus - Certified;cULus - Listed