



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S12430 12.5A19/CL/Led/E26/930/120V

Satco

Catalog Number	S12430
Manufacturer	Satco
Description	12.5 Watt Led A19 Lamp - Clear Medium Base 3000K 90 Cri 120 Volts
Weight per unit	0.0900 (lbs/each)
Product Category	20230120112515

Features

average life	15000
Base	E26
beam angle	320
dimnable	Yes-Dimmable
lumens	1500
Material	Glass; Aluminum
Power Factor	0.7
Shape	A19
Voltage Rating	120
Warranty	3 Year Limited
Wattage	12.5

Material, Color, and Finish

color rendering index (cri)	90+
color temperature	3000
Finish	Clear

Dimensions and Weight

Size	4.41
------	------

Descriptions

Description	12.5A19/CL/LED/E26/930/120V
extra long description	SATCO S12430 12.5A19/CL/LED/E26/930
Long Description	12.5 Watt LED A19 Lamp - Clear Medium Base 3000K 90 CRI 120 Volts
Product Type	12.5A19/CL/Led/E26/930/120V
Special Features	Warranty: 2-Years ; Location Rating: Wet ; Operating Temp: -20C (-4F) to +40C (+104F) ; Material: Aluminum / Glass ; Indoor Outdoor: Indoor;Outdoor ; Color Temp: Soft White ; Efficacy: 120.00 LPW ; Candle Power: 100 ; DLC Approved: False ; FCC Compliant: True ; Indoor Outdoor: Indoor;Outdoor ; Lamp Filament: LED Filament ; ANSI Base: E26 ; Amps: 0.104A



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Satco
Manufacturers Part Number	S12430

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	LED General Service

Packaging

Carton	1
Weight	0.09
Weight Per each	0.09

Uses, Certifications, and Standards

Application	LED
Operating Temperature	-20C (-4F) to a maximum of +40C (+104F)
standard	cULus - Certified;cULus - Listed