



Project / Job Name: \_\_\_\_\_

Location: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Notes: \_\_\_\_\_

**S13175** - 30/70/100/120 Watt LED Work Light with Remote; 5000K CCT; Red Finish; 120 Volt



**GENERAL**

Company	SATCO
EA Height	15.08
EA Width	7.36
EA Length	7.76
Bulb Included	Integrated
CA Regulations	T20 Exempt - Fixtures Not Regulated
Diameter	5.07
Dimmable Text	Dimmable with Remote
Material	Aluminum / Plastic
Fixture Type	Work Light
Includes	Safety Cable Mount Kit; Remote Control
Product Notes	Remote require 2 x AAA 1.5V battery (not provided).
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 4KV
Total Harmonic Distortion	<20%
Cct Selectable	False
Wattage Selectable	True
Finish Family	Red
Amps	0.250/0.583/0.833/1.000A
Has Camera	False
IOT Enabled	False
Lens Finish	Clear
Lens Material	Polycarbonate (PC)
Connectable Units	8
Power Factor	>0.9
Indoor Outdoor	Indoor and Outdoor
Product Technology	LED

**ELECTRICAL**

CCT (Kelvin Temp)	5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	180/280/360
Color Temp	Natural Light
CRI	80+
Dimming Type	Step Dimming
Operating Frequency	50/60Hz
Operating Temp	-40C (-40F) to +40C (+104F)
HID Equivalent	400W
Lumens	5370L/12395L/17025L/19820L
Volts	120v
Watts	30W/70W/100W/120W

**PHYSICAL**

Lamp Base	Plug
Finish	Red
ANSI Base	Plug
Lamp Type	Integrated LED

**ADDITIONAL INFO**

Warranty	5-Years
----------	---------

**PACKAGING**

UPC	045923131752
Case Cube	2.2985
Case Height	15.87
Case Length	16.22
Case Quantity	4
Case UPC	10045923131759
Case Weight	30.36
Case Width	15.43
EA Cube	0.4984
EA Height	15.08
EA Length	7.76
EA Quantity	1
EA Weight	6.6
EA Width	7.36
Inner Cube	0
Pack Type	Box
Web Height	12.58
Web Width	5.07

**COMPLIANCE**

CA Prop 65	Lead
FCC Compliant	True
IP Rating	IP64
Location Rating	Damp
ROHS Compliant	Yes
Safety Listing	cULus - Listed
Title 20	Exempt
T24 Compliant	False