



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S18400 4.5 Watt Led PL 2-Pin 27K G23 120-277V Type-B BB

Satco

Catalog Number	S18400
Manufacturer	Satco
Description	Satco S18400 4.5W/Led/CFL/827/G23/B
Weight per unit	0.5500 (lbs/each)
Product Category	Lighting

### Features

average life	50000
Base	G23
beam angle	360
dimmable	Non-Dimmable
lumens	450
Material	Plastic
Power Factor	0.9
Shape	PL
Voltage Rating	120 to 277
Warranty	5 Year Limited - 10 hr per day
Wattage	4.5

### Material, Color, and Finish

color rendering index (cri)	80+
color temperature	2700
Finish	Frosted

### Descriptions

Description	4.5 WATT LED PL 2-PIN 27K G23 120-277V TYPE-B BB
Long Description	SATCO S18400 4.5W/LED/CFL/827/G23/B
Product Type	4.5W/Led/CFL/827/G23/BP
Special Features	Warranty: 5-Years ; Location Rating: Damp ; Operating Temp: -25C (-13F) to +45C (+113F) ; Material: Plastic ; Surge Protection: Built-in-surge protection - 0.5KV ; Color Temp: Warm White ; Efficacy: 100.00 LPW ; DLC Approved: False ; FCC Compliant: True ; Lamp Filament: LED ; ANSI Base: G23 ; Lamp Ballast Type AB: Type B ; Amps: 0.038-0.016A ; T24 Compliant: False

### Manufacturer Information

Brand	Satco
GTIN	00045923184000
Manufacturers Part Number	S18400
UPC	045923184000



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	LED PLUG-IN (REPLACEMENT FOR CFL BIAX LAMPS)
Type	LED PL

## Packaging

Carton	1
Package	10
Weight	0.55
Weight Per each	0.55

## Uses, Certifications, and Standards

Application	LED
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)
standard	cETLus - Classified