



S1914

50Q/F/MC

50 watt; Halogen; T4; Frosted; 2000 Average rated Hours; 675 Lumens; Mini Cand base; 120 volts

Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output



S1914

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S1914	045923019142	50	T4	Mini Cand	E11	50Q/F/MC	120

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color	Average Rated Hours
Frost	2 1/16"	0.50"	CC-2V	675	2900	Warm White	2000

Pack	Package Type	RoHS Compliant
480/12	Box	Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S1914

50Q/F/MC

50 watt; Halogen; T4; Frosted; 2000 Average rated Hours; 675 Lumens; Mini Cand base; 120 volts

Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output



S1914

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S1914	045923019142	50	T4	Mini Cand	E11	50Q/F/MC	120

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color	Average Rated Hours
Frost	2 1/16"	0.50"	CC-2V	675	2900	Warm White	2000

Pack	Package Type	RoHS Compliant
480/12	Box	Yes



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

