

# Specifications



Photo is representative



## Eaton S20N11P01P

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 67P, 60 Hz, 180C, 1 kVA, 1 kVA, wall, single-phase, 240 V, 480 V, 120/240 V, NEMA ST-20, NONE, 115 °C rise, 1 KVA, indoor-outdoor, 3A

### General specifications

<b>PRODUCT NAME</b>	Eaton General purpose encapsulated transformer
<b>CATALOG NUMBER</b>	S20N11P01P
<b>UPC</b>	786680073687
<b>PRODUCT LENGTH/DEPTH</b>	6.56 in
<b>PRODUCT HEIGHT</b>	13.03 in
<b>PRODUCT WIDTH</b>	5.53 in
<b>PRODUCT WEIGHT</b>	25 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

Physical Attributes	
COIL MATERIAL	Copper
DESIGN	EP
ENCLOSURE	NEMA 3R
FRAME	67P
INSULATION	180 °C
MOUNTING	Wall
TAP SIZE	None
TYPE	General-Purpose Encapsulated Transformer
WIRING CONNECTION	3A

Miscellaneous	
WEATHERSHIELD	Indoor-Outdoor

Performance Ratings	
FREQUENCY RATING	60 Hz
KVA RATING	1 kVA
KVA	1 kVA
PHASE	Single-phase
PRIMARY VOLTAGE	240 V, 480 V
SECONDARY VOLTAGE	120/240 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	1 kVA

Resources	
CATALOGS	<a href="#">Commercial Distribution, Transformers, Volume 2, Tab 2</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - S20N11P01P</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



**Eaton Corporation plc**  
 Eaton House  
 30 Pembroke Road  
 Dublin 4, Ireland  
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton S20N11P01P

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 67P, 60 Hz, 180C, 1 kVA, 1 kVA, wall, single-phase, 240 V, 480 V, 120/240 V, NEMA ST-20, NONE, 115 °C rise, 1 KVA, indoor-outdoor, 3A

### General specifications

<b>PRODUCT NAME</b>	Eaton General purpose encapsulated transformer
<b>CATALOG NUMBER</b>	S20N11P01P
<b>UPC</b>	786680073687
<b>PRODUCT LENGTH/DEPTH</b>	6.56 in
<b>PRODUCT HEIGHT</b>	13.03 in
<b>PRODUCT WIDTH</b>	5.53 in
<b>PRODUCT WEIGHT</b>	25 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed

## Physical Attributes

COIL MATERIAL	Copper
DESIGN	EP
ENCLOSURE	NEMA 3R
FRAME	67P
INSULATION	180 °C
MOUNTING	Wall
TAP SIZE	None
TYPE	General-Purpose Encapsulated Transformer
WIRING CONNECTION	3A

## Miscellaneous

WEATHERSHIELD	Indoor-Outdoor
---------------	----------------

## Performance Ratings

FREQUENCY RATING	60 Hz
KVA RATING	1 kVA
KVA	1 kVA
PHASE	Single-phase
PRIMARY VOLTAGE	240 V, 480 V
SECONDARY VOLTAGE	120/240 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	1 kVA

## Resources

CATALOGS	<a href="#">Commercial Distribution, Transformers, Volume 2, Tab 2</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - S20N11P01P</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

