

Eaton General purpose encapsulated transformer

S20N11P01P

UPC:786680073687

Dimensions:

- **Height:** 13.03 IN
- **Length:** 6.56 IN
- **Width:** 5.53 IN

Weight:25 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** General-Purpose Encapsulated Transformer
- **Design:** EP
- **Coil Material:** Copper
- **Enclosure:** NEMA 3R
- **Frame:** 67P
- **Frequency Rating:** 60 Hz
- **Insulation:** 180C
- **Kva Rating:** 1 kVA
- **Mounting:** Wall
- **Phase:** Single-phase
- **Primary Voltage:** 240 V, 480 V
- **Secondary Voltage:** 120/240 V
- **Sound Level:** NEMA ST-20
- **Tap Size:** NONE
- **Temperature Rise:** 115 °C rise
- **Volt Ampere Rating:** 1 KVA
- **Weathershield:** Indoor-Outdoor
- **Wiring Connection:** 3A

Supporting documents:



- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - S20N11P01P](#)

Certifications:

- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.