

Eaton S20N11P01P

Catalog Number: S20N11P01P

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 67P, 60 Hz, 180C, 1 kVA, 1 kVA, wall, single-phase, 240 V, 480 V, 120/240 V, NEMA ST-20, NONE, 115 °C rise, 1 KVA, indoor-outdoor, 3A

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S20N11P01P
	UPC
	786680073687
Product Length/Depth	Product Height
6.56 in	13.03 in
Product Width	Product Weight
5.53 in	25 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Copper

Design

EP

Enclosure

NEMA 3R

Frame

67P

Insulation

180 °C

Mounting

Wall

Tap size

None

Type

General-Purpose Encapsulated Transformer

Wiring connection

3A

Miscellaneous

Weathershield

Indoor-Outdoor

Performance Ratings

Frequency rating

60 Hz

Kva Rating

1 kVA

kVA

1 kVA

Phase

Single-phase

Primary voltage

240 V, 480 V

Secondary Voltage

120/240 V

Sound Level

NEMA ST-20

Temperature rise

115 °C rise

Volt ampere rating

1 kVA

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - S20N11P01P



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)