Eaton S20N11S25N

Catalog Number: S20N11S25N

Eaton, general purpose encapsulated transformer, ep, single-phase, pv: 240 x 480v, taps: none, sv: 120/240v, 115°c, 25 kva, al windings, frame: 182, indoor-outdoor-

General specifications



Product Name

Catalog Number

Eaton General purpose encapsulated

S20N11S25N

transformer

UPC

786680108839

Product Length/Depth

Product Height

20 in

20.2 in

Product Width

Product Weight

25 in

385 lb

Warranty

Certifications

Eaton Selling Policy 25-000, one (1) year UL Listed

from the date of installation of the

Catalog Notes

Product or eighteen (18) months from the

Model N

date of shipment of the Product,

WIOC

whichever occurs first.

Photo is representative



Physical Attributes

Coil material

Aluminum

Design

ΕP

Enclosure

NEMA 3R

Frame

182

Tap size

None

Type

General-Purpose Encapsulated Transformer

Wiring connection

ЗА

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

240 V, 480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

25 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - S20N11S25N

Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.













