



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S21227 4.5W Led G25 30K CLR Med Base 90CRI 120V

Satco

Catalog Number	S21227
Manufacturer	Satco
Description	4.5 Watt G25 Led Lamp - Clear - Medium Base - 90 Cri - 3000K - 120 Volts
Weight per unit	0.1700 (lbs/each)
Product Category	Lighting

Features

average life	15000
Base	E26
beam angle	300
dimmable	Yes-Dimmable
lumens	350
Power Factor	0.77
Shape	G25
Voltage Rating	120
Wattage	4.5

Material, Color, and Finish

color rendering index (cri)	90+
color temperature	3000
Finish	Clear

Dimensions and Weight

Size	4.45
------	------

Descriptions

Description	4.5W LED G25 30K CLR MED BASE 90CRI 120V
extra long description	SATCO S21227 4.5G25/LED/CL/930/120V
Long Description	4.5 Watt G25 LED Lamp - Clear - Medium Base - 90 CRI - 3000K - 120 Volts
Product Type	4.5G25/Led/CL/930/120V
Special Features	Warranty: 2-Years ; Location Rating: Wet ; Operating Temp: -20C (-4F) to +45C (+113F) ; Dimmable Text: 120V only ; Material: Glass / Nickel Plated Aluminum ; Indoor Outdoor: Indoor;Outdoor ; Color Temp: Soft White ; Efficacy: 77.78 LPW ; DLC Approved: False ; FCC Compliant: True ; NSF Approved: No ; Indoor Outdoor: Indoor;Outdoor ; Lamp Filament: LED Filament ; ANSI Base: E26 ; Amps: 0.048A



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Satco
GTIN	00045923205422
Manufacturers Part Number	S21227
UPC	045923205422

Taxonomies, Classifications, and Categories

Category Description	LED DECORATIVE C, CA, F, G SHAPE LAMPS
Type	LED General Service

Packaging

Carton	1
Weight Per each	0.17

Uses, Certifications, and Standards

Application	LED
standard	cULus - Certified;cULus - Listed