## SATCO NUVO

Project Name

Prepared By



## Notes

General	
Status	Active
Watts	5.5W
Incandescent Equivalent	60W
Volts	120V
Shape	CA10
Base	Candelabra
ANSI Base	E12
Finish	Clear
CCT (Kelvin)	3000K
Temperature	Warm White
CRI	90
Lumens	500L
Beam Spread	300
Dimmable	Yes-Dimmable
Hours Rated	15000
Technology	LED
Electrical	
Operating Frequency	60 Hz
Power Factor	>0.7
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
Physical	
MOL	4.72
MOD	1.38
Weight (lb.)	0.035
Additional Information	
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited
Compliance	
Safety Listing	cETLus
Location Rating	Wet
Energy Star	Pending
CA T20 / T24 Rationale	T20 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale









