## SATCO NUVO

Project Name

Location

Prepared By



www] 03-07-2022 02:41:0

| General                    |   |
|----------------------------|---|
| Status                     | Active  |
| Watts                      | 80W   |
| HID Equivalent             | 320W  |
| Volts                      | 100V-277V   |
| Base                       | Extended Mogul  |
| ANSI Base                  | EX39  |
| Finish                     | White   |
| CCT (Kelvin)               | 3000K/4000K/5000K                                     |
| CRI                        | 80  |
| Lumens                     | 7560L/8820L/11200L                                    |
| Beam Spread                | 360   |
| Dimmable                   | Yes-Dimmable  |
| Hours Rated                | 50000   |
| Lamp Type                  | Corncob   |
| Technology                 | LED   |
| Min Compartment Size       | Length: 9.85 in. Width: 9.85 in.<br>Height: 10.95 in. |
| Ballasting Requirements    | Ballast Bypass  |
| Electrical                 |   |
| Operating Frequency        | 50-60 Hz  |
| Operating Frequency        | Dimmable only via the                                 |
| Dimming Note               | wattage/lumen selectable dial included on lamp        |
| Power Factor               | >0.9  |
| Burning Position           | Base Up or Base Down Only                             |
| Surge Protection           | Built-in surge protection - 4KV                       |
| Operating Temperature      | -30C (-22F) to a maximum of +45C (+113F)              |
| Physical                   |   |
| MOL                        | 9.96  |
| MOD                        | 5.11  |
| Lens Material              | Plastic   |
| Housing Color              | Dark Gray   |
| Weight (lb.)               | 2.68  |
|                            |   |
| Additional Information     |   |
| Additional Info            | Power selectable                                      |
| Rated For Enclosed Fixture | Yes   |
| IP Rating                  | IP64  |
| Warranty                   | 5 Year Limited - 12 hr per day                        |
| Compliance                 |   |
| Safety Listing             | cULus listed; cULus classified                        |
| Location Rating            | Damp  |
| Energy Star                | No  |
| CA T20 / T24 Rationale     | Exempt - Base Not Regulated                           |
| RoHS Compliant             | Yes   |
| FCC Compliant              | Yes   |
| SDS Shoot                  | LED Lamp  |

SDS Sheet

LED\_Lamp

Copyright 2020 Satco Products, Inc. All Rights Reserved

For More Information visit: http://www.satco.com/







