



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## S26565 20W T12 24" 41K Med Bi-Pin Base 62 Cri 1200LM

Satco

Catalog Number	S26565
Manufacturer	Satco
Description	20 Watt - Fluorescent T12 - 4100K - Medium Bi-Pin (G13) Base
Weight per unit	0.3700 (lbs/each)
Product Category	Lighting

### Features

average life	10000
beam angle	360
lumens	1200
Shape	T12
Socket Type	G13
Wattage	20

### Material, Color, and Finish

Color	White
color rendering index (cri)	60+
color temperature	4100
Finish	white

### Dimensions and Weight

Diameter	1.5
Length	23.22

### Descriptions

Description	20W T12 24" 41K MED BI-PIN BASE 62 CRI 1200LM
extra long description	SATCO S26565 F20T12/CW
Long Description	20 Watt - Fluorescent T12 - 4100K - Medium Bi-pin (G13) Base
Product Type	F20T12/CW
Special Features	ANSI Base: G13;Color Temp: Cool White;DLC Approved: False;Efficacy: 60.00 LPW;Hg Content: 7.9;Operating Temp: Ballast Dependent;T24 Compliant: False;Warranty: 3-Years

### Manufacturer Information

Brand	Satco
GTIN	00045923265655
Manufacturers Part Number	S26565
UPC	045923265655

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	Fluorescent Linear



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton ..... 30

Weight ..... 0.0049

Weight Per each ..... 0.37

## Uses, Certifications, and Standards

Application ..... Fluorescent

standard ..... Unlisted