

Project Name

Location

Prepared By



# SATCO S26565

F20T12/CW

## General

Status	Active
Watts	20W
Shape	T12
Base	Medium Bi Pin
ANSI Base	G13
Finish	White
CCT (Kelvin)	4100K
Temperature	Cool White
CRI	62
Lumens	1200L
Beam Spread	360
Hours Rated	10000
Lamp Type	Linear
Technology	Fluorescent

## Electrical

Hg Content	< 8 mg
------------	--------

## Physical

MOL	23.22
MOD	1.50
Weight (lb.)	0.0049

## Compliance

Energy Star	No
California Status	Lawful for sale
SDS Sheet	Linear_Fluorescent_Lamp

## Notes

[www] 11-29-2021 04:01:43