

Project Name

Location

Prepared By



Notes

[www] 10-20-2020 00:00:00

**General**

Status	Active
Watts	6.5
Incandescent Equivalent	50
Fluorescent Equivalent	11.00
Volts	120V
Shape	PAR20
Base	Medium
ANSI Base	E26
Finish	Silver
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	90
Lumens	520
Beam Spread	25
Dimmable	Yes - Dimmable
Hours Rated	25000
Lamp Type	PAR
Technology	LED

**Electrical**

Operating Frequency	60 Hz
CBCP	1179
Dimming Type	Thyristor
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

**Physical**

MOL	2.99
MOD	2.44
Lensed	Lensed Lamp
Lens Finish	Clear
Lens Material	Thermo Plastic
Housing Color	Silver

**Additional Information**

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 12 hr per day

**Compliance**

Safety Listing	cULus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	2366322
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

