SATCO NUVO

Project Name

Location

Prepared By



SATCO S29446

15PAR38/LED/40'/930/120V

Notes

www] 01-28-2021 11:42:0

General	
Status	Active
Watts	15
Incandescent Equivalent	90
Fluorescent Equivalent	23.00
Volts	120V
Shape	PAR38
Base	Medium
ANSI Base	E26
Finish	Silver
CCT (Kelvin)	3000
Temperature	Warm White
CRI	90
Lumens	1200
Beam Spread	40
Dimmable	Yes - Dimmable
Hours Rated	25000
Lamp Type	PAR
Technology	LED

Electrical	
Operating Frequency	60 Hz
CBCP	1533
Dimming Type	Thyristor
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical	
MOL	5.00
MOD	4.72
Lensed	Lensed Lamp
Lens Finish	Clear
Lens Material	Thermo Plastic
Housing Color	Silver
Weight (lb.)	0.34

Additional Information	
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 12 hr per day
Compliance	

Compliance	
Safety Listing	cULus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2367566
California Status	California T24 Compliant
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
FCC Compliant	Yes









SDS Sheet

LED_Lamp





