



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1010 SE 1st Street
73501-0000, OK Lawton
Phone: 580-581-7270
Fax: 580-215-4548



S29752 *Delisted* 60W Led Hid RPL (Adj LT PNLS)

Satco

Catalog Number	S29752
Manufacturer	Satco
Description	Led Hid Lamp, Corncab Shape, 300 ° Beam Angle, 5000 K, 5200 LM Brightness (Lumens), 60 W, 100 to 277 V Ac, White, 50000 H Average Life, Mogul Base, Non Dimmable, 3.81 In Diameter, 8.56 In Height, 5 Yr Warranty, 2.45 LB
Weight per unit	2.9 (lbs/each)
Product Category	Hid High Intensity Discharge L

Features

connection	Mogul Extended
Fixture Type	Corncob Lamp
lumens	5.2k
surge protection	Built-in surge protection - 2.5KV

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Size	MOL: 8.56, MOL: 3.81
------	----------------------

Descriptions

Description	*DELISTED* 60W LED HID RPL (ADJ LT PNLS)
Special Features	Burning Position: Universal ; CEC: Exempt - Base Not Regulated ; Dimmable: Non-Dimmable ; Minimum Compartment Size: Width 9.25 in. Length 9.25 in. Depth 8.27 in. ; Operating Temp: -20C (-4F) to a maximum of +40C (+104F) ; Temperature (K): 5000 ; Color Temperature: Natural Light ; 360 degree beam spread ; Incandescent Equivalence: 500 ; Fluorescent Equivalence: 85 ; 5 Year Limited Warranty

Manufacturer Information

GTIN	00045923297526
sub brand	Satco
UPC	045923297526

Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
Type	LED HID Replacement

Availability

Manufacturer Status	Inactive
---------------------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1010 SE 1st Street
73501-0000, OK Lawton
Phone: 580-581-7270
Fax: 580-215-4548

Packaging

Carton	12
Package	1
Weight Per each	2.88

Uses, Certifications, and Standards

Operating Temperature	-20C (-4F) to a maximum of +65C (+149F)
standard	cULus Listed Wet