

Project Name

Location

Prepared By



SATCO S29806

2.5/LED/T19/FLAME/816/120V/E26

Notes

[www] 12-26-2022 03:53:14

General

Status	Active
Watts	2.5W
Incandescent Equivalent	25W
Volts	120V
Shape	T19
Base	Medium
ANSI Base	E26
Finish	White
CCT (Kelvin)	1600K
CRI	60
Lumens	150L
Dimmable	Non-Dimmable
Hours Rated	10000
Technology	LED

Smart Product Info

IOT Enabled	No
-------------	----

Electrical

Operating Frequency	60 Hz
Power Factor	0.4
Burning Position	Base Up or Down
Operating Temperature	-20C (-4F) to +40C (+104F)

Physical

MOL	4.88
MOD	2.36
Housing Color	White
Weight (lb.)	0.14

Additional Information

Additional Info	8 piece retail ready counter display tray available.
Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cULus - Listed
Location Rating	Damp
Energy Star	No
CA T20 / T24 Rationale	Exempt - < 2200K
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
SDS Sheet	LED_Lamp