

\$29811 A19 LED 11A19/LED/3000K/1100L/120V/D

Lamp Type	LED			
Bulb Type	A19			
Base Type	E26			
Wattage	11			
Color Temperature	3000			
Color Rendering Index CRI	80			
Warranty	3 Year Limited			



Lighting Facts Per Bulb

Brightness	1100 lumens
Estimated Energy Cost	\$1.32 <u>@</u>
per year, based on 3 hrs Energy cost depends on use.	• .
Average Life	22.8 years
Based on 3 hrs/day	
Light Appearance	e
Warm	Cool
3000 K	
Energy Used	11 watts

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29811	LED	*20045923298114	120	11	75	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non- Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	11A19/LED/3000	K/1100LY16280V/D	n/a	4 3/8	2 3/8	1100	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
3000	Warm White	80	220	24	Box	Yes	Yes