

## \$29812 A19 LED 11A19/LED/4000K/1100L/120V/D

Lamp Type	LED
Bulb Type	A19
Base Type	E26
Wattage	11
Color Temperature	4000
Color Rendering Index CRI	80
Warranty	3 Year Limited



## Lighting Facts Per Bulb

Brightness	1100 lumens				
Estimated Energy Cost	\$1.32				
per year, based on 3 hr. Energy cost depends on use.	• •				
Average Life	22.8 years				
Based on 3 hrs/day					
Light Appearance	e				
Warm	Cool				
4000 K					
Energy Used	11 watts				

## **Product Specifications**

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29812	LED	*20045923298121	120	11	75	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non- Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	11A19/LED/4000	K/1100LY16280V/D	n/a	4 3/8	2 3/8	1100	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
4000	Cool White	80	220	24	Box	Yes	Yes