



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S29816 15W Led A19 30K FRST E26

Satco

Catalog Number	S29816
Manufacturer	Satco
Description	A19 Led Lamp, 220 ° Beam Angle, 3000 K, 1600 LM Brightness (Lumens), 15 W, 120 V, Frosted White, 25000 H Average Life, Medium Base, Dimmable, 2.38 In Diameter, 4.63 In Length, 0.96 Power Factor, -4 °F Operating Temperature, +113 °F Operating Temperature, 0.31 LB
Weight per unit	0.3500 (lbs/each)
Product Category	Led A-Line A Shape Lamps

Features

connection	Medium
Fixture Type	Type A
lumens	1.6k
Voltage Rating	120
Warranty	5 Year Limited - 10 hr per day

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Size	MOL:4.63,MOD:2.38
------	-------------------

Descriptions

Description	15W LED A19 30K FRST E26
extra long description	SATCO S29816 15A19/LED/3000K/1600L/
Special Features	CEC: Non-Compliant - Not 82 CRI ; Dimmable: Yes Dimmable ; Grouping: LED Other OMNI 1707 ; Operating Temp: -20C (-4F) to a maximum of +45C (+113F) ; Color Temperature: Warm White ; Kelvin Temperature: 3000 ; CRI: 80 ; Energy Star: Yes ; Dimmable: Yes ; Enclosed Lamp: Yes ; Warranty: 5 Year Limited

Manufacturer Information

GTIN	00045923298165
UPC	045923298165

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
Type	LED

Packaging

Carton	24
Package	6
Weight Per each	0.35



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)
standard	cULus damp location rated