



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S29839 9.8W Led A19 50K 800LM Dim

Satco

Catalog Number	S29839
Manufacturer	Satco
Description	9.8A19/Omni/220/Led/50K
Weight per unit	0.1900 (lbs/each)
Product Category	Led A-Line A Shape Lamps

Features

Energy Star	yes
-------------	-----

Descriptions

Description	9.8W LED A19 50K 800LM DIM
extra long description	DIMMABLE TYPE; 4-1/2 INCH; UL/ETL, UL (CANADA AND US) APPROVAL; TOTALLY ENCLOSED FIXTURE, DAMP LOCATION APPLICATION; 120 V VOLTAGE RATING; 2.38 INCH DIAMETER; 9.8 W WATTAGE; LED LAMP; E26 MEDIUM BASE TYPE; 25000 LIFE IN HOUR; A19 SHAPE DESIGNATION; 5000; 80 COLOR RENDERING INDEX; FROSTED GLASS FINISH; NATURAL LIGHT GLASS COLOR; A-LINE SHAPE DESCRIPTION; 220 DEGREE BEAM SPREAD ANGLE; ROHS COMPLIANT; INITIAL INTENSITY 800 LUMEN; POWER FACTOR 0.98; OPERATING TEMPERATURE -20 TO 45 DEG C; PACKAGING QUANTITY 24
Long Description	9.8A19/OMNI/220/LED/50K
Product Type	A-Line Led Lamp

Manufacturer Information

Brand	Satco
GTIN	00045923298394
Manufacturers Part Number	S29839
UPC	045923298394

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
----------------------	------------------------

Packaging

Carton	1
Weight Per each	0.19