

S29841 A19 LED

9.8A19/OMNI/220/LED/35K/GU24

Lamp Type	LED
Bulb Type	A19
Base Type	GU24
Wattage	9.8
Color Temperature	3500
Color Rendering Index CRI	80
Warranty	3 Year Limited



Lighting Facts Per Bulb

Brightness 800 lumens

Estimated Energy Cost \$1.08

per year, based on 3 hrs/day, 11c/kWh.
Energy cost depends on utility rates and light use.

Average Life 22.8 years

Based on 3 hrs/day

Light Appearance



Energy Used 9 watts

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29841	LED	*20045923298411	120	9.8	60	A19	GU24
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
GU24	9.8A19/OMNI/220/LED/35K	Yes	n/a	4 3/16	2 3/8	800	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
3500	Neutral White	80	220	24	Box	Yes	Yes

S29841 A19 LED

9.8A19/OMNI/220/LED/35K/GU24

Lamp Type	LED
Bulb Type	A19
Base Type	GU24
Wattage	9.8
Color Temperature	3500
Color Rendering Index CRI	80
Warranty	3 Year Limited



Lighting Facts Per Bulb

Brightness 800 lumens

Estimated Energy Cost \$1.08

per year, based on 3 hrs/day, 11c/kWh.
Energy cost depends on utility rates and light use.

Average Life 22.8 years

Based on 3 hrs/day

Light Appearance



Energy Used 9 watts

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29841	LED	*20045923298411	120	9.8	60	A19	GU24
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
GU24	9.8A19/OMNI/220/LED/35K	Yes	n/a	4 3/16	2 3/8	800	25000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
3500	Neutral White	80	220	24	Box	Yes	Yes