



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1026 North Collins Blvd
70433-0000, LA Covington
Phone: 985-302-3016
Fax: 985-249-6076



S29866 3.5W 50K Led BLNT Candelabra

Satco

Catalog Number	S29866
Manufacturer	Satco
Description	Satco S29866 4W CTC/Led/50K/CL/120V
Weight per unit	0.0200 (lbs/each)
Product Category	Led Decorative C, Ca, F, G Sha

Features

average life	15000
connection	Candelabra
Fixture Type	LED Filament
lumens	350
Shape	C11
Voltage Rating	120
Warranty	3 Year Limited
Wattage	4

Material, Color, and Finish

Color	Colorless
-------	-----------

Dimensions and Weight

Size	MOL: 3.88, MOD: 1.38
------	----------------------

Descriptions

Description	3.5W 50K LED BLNT CANDELABRA
Long Description	SATCO S29866 4W CTC/LED/50K/CL/120V
Product Type	4W CTC/Led/50K/CL/120V
Special Features	CEC: Non-Compliant - Not 82 CRI ; Dimmable: Yes Dimmable ; Operating Temp: -20C (-4F) to a maximum of +45C (+113F) ; 5000K color temperature ; 80 CRI ; 360 degree beam spread ; Enclosed lamp rated ; 3 Year Limited Warranty

Manufacturer Information

Brand	Satco
GTIN	00045923298660
Manufacturers Part Number	S29866
sub brand	Satco
UPC	045923298660

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	LED



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1026 North Collins Blvd
70433-0000, LA Covington
Phone: 985-302-3016
Fax: 985-249-6076

Availability

Manufacturer Status Inactive

Packaging

Carton 1

Weight Per each 0.02

Uses, Certifications, and Standards

Operating Temperature -20C (-4F) to a maximum of +45C (+113F)

standard cULus damp location rated