



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S29915 4' T8 Led 4000K Bal Bypas

Satco

Catalog Number	S29915
Manufacturer	Satco
Description	Satco S29915 14T8/Led/48-840/BP 120
Weight per unit	0.5600 (lbs/each)
Product Category	20181210121855

Features

average life	50000
Base	Medium Bi Pin
beam angle	210
dimmable	No
lumens	1.8k
Shape	T8
Voltage Rating	277
Warranty	5 Year Limited - T8 LED Bulbs - Ballast Bypass
Wattage	14

Material, Color, and Finish

color temperature	4000
-------------------	------

Dimensions and Weight

Diameter	1
Length	48

Descriptions

Description	4' T8 LED 4000K BAL BYPAS
Long Description	SATCO S29915 14T8/LED/48-840/BP 120
Product Type	14T8/Led/48-840/BP 120-277V
Special Features	Lawful for sale in California ; Dimmable: Non-Dimmable ; Operating Temp: -20C (-4F) to a maximum of +45C (+113F) ; Safety Listing: cULus Classified - Damp ; SDS Class: LED_Lamp ; Fluorescent Equivalence: 25-32 watts ; Lamp Appearance: Frosted ; Warranty: 5 Year Limited

Manufacturer Information

Brand	Satco
GTIN	00045923299155
Manufacturers Part Number	S29915
sub brand	Satco
UPC	045923299155



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description.....Fuses & Fuse Accessories

Type.....LED T8

Availability

Manufacturer Status.....Inactive

Packaging

Carton.....1

Weight Per each.....0.56

Uses, Certifications, and Standards

Operating Temperature.....-20C (-4F) to a maximum of +45C (+113F)