



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S29916 14W Led T8 48" 50K 120-277V *Satco*

Catalog Number	S29916
Manufacturer	Satco
Description	Satco S29916 14T8/Led/48-850/BP 120
Weight per unit	0.5616 (lbs/each)
Product Category	Lighting

Features

average life	50000
Base	Medium Bi Pin
beam angle	210
dimmable	No
lumens	1.8k
Shape	T8
Voltage Rating	277
Warranty	5 Year Limited - T8 LED Bulbs - Ballast Bypass
Wattage	14

Material, Color, and Finish

color temperature	5000
-------------------	------

Dimensions and Weight

Diameter	1
Length	48

Descriptions

Description	14W LED T8 48" 50K 120-277V
Long Description	SATCO S29916 14T8/LED/48-850/BP 120
Product Type	14T8/Led/48-850/BP 120-277V
Special Features	Lawful for sale in California ; Dimmable: Non-Dimmable ; Operating Temp: -20C (-4F) to a maximum of +45C (+113F) ; Safety Listing: cULus Classified - Damp ; SDS Class: LED_Lamp ; Fluorescent Equivalence: 25-32 watts ; Lamp Appearance: Frosted ; Warranty: 5 Year Limited

Manufacturer Information

Brand	Satco
GTIN	00045923299162
Manufacturers Part Number	S29916
sub brand	Satco
UPC	045923299162



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	LED T8

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Weight Per each	0.5616

Uses, Certifications, and Standards

Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
-----------------------	---