

\$29936 T8 LED 12T8/LED/48-840/DR

Lamp Type	LED
Bulb Type	Т8
Base Type	G13
Wattage	12
Color Temperature	4000
Color Rendering Index CRI	82



Lighting Facts Per Bulb

Brightness	1800 lumens					
Estimated Energy Cost	\$1.45					
per year, based on 3 hr Energy cost depends o use.	**					
Average Life	45.7 years					
Based on 3 hrs/day						
Light Appearance	ce					
Warm	Cool					
	4000 K					
Energy Used	12 watts					

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S29936	LED	*	n/a	12	n/a	Т8	Medium Bi Pin
ANSI Base	Lamp Code	Dimmable/Non- Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
G13	12T8/LED/48- 840/DR	n/a	n/a	48	1	1800	50000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
4000	Cool White	82	210	10	sleeve	n/a	Yes