



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9707 Broadway St Suite 100
78217-0000, TX San Antonio
Phone: 210-646-6950
Fax: 210-646-6192



S3713TRBK Recept.15A 125V TR Clock HNGR Recessed W/Plate, BK *Pass & Seymour/Legrand*

Catalog Number	S3713TRBK
Manufacturer	Pass & Seymour/Legrand
Description	Tamper-Resistant Clock Hanger Recessed Receptacle With Smooth Wall Plate 15A, 125V. For Detailed Tamper-Resistant Receptacle Information, Visit Our Tamper-Resistant Receptacles Page.
Weight per unit	N/A
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15
indoor/outdoor	Indoor
media	Yes
Number of Wires	3
Outlet Type	Straight Blade, Tamper-Resistant
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	YES
Wire Size	14 - 10

Dimensions and Weight

Size	5"
------	----

Descriptions

Description	RECEPT.15A 125V TR CLOCK HNGR RECESSED W/PLATE, BK
extra long description	P&S S3713TRBK RECP RECESS TR 15A/12
Features	Recessed
Long Description	Tamper-Resistant Clock Hanger Recessed Receptacle with Smooth Wall Plate 15A, 125V. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.
Product Type	Recp Recess TR 15A/125V W/Plate BK
Special Features	Dust & moisture resistant, clock hanger receptacle, cellular neoprene sealing mat fits under wall plate

Manufacturer Information

Brand	Pass & Seymour/Legrand
GTIN	00785007180183
Manufacturers Part Number	S3713TRBK
UPC	785007180183



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9707 Broadway St Suite 100
78217-0000, TX San Antonio
Phone: 210-646-6950
Fax: 210-646-6192

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Outlet

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0

Uses, Certifications, and Standards

Application	Commercial
Mounting	WALL
nema rating	5-15R
standard	CULUS, UL 498