



## TAMPER-RESISTANT CLOCK HANGER RECEPTACLES, RECESSED WITH SMOOTH WALL PLATE, 15A, 125V, WHITE

S3713TRW | [Pass & Seymour](#)

### FEATURES & BENEFITS

Tamper-Resistant Clock Hanger Recessed Receptacle with Smooth Wall Plate 15amp 125volt, White

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



- Single recessed receptacle.
- Smooth wall plate.

### SPECIFICATIONS

#### GENERAL INFO

Color: White  
Type: Clock Hanger  
Special Features: Clock Hanger  
Style: Decorator, Smooth

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listed: Yes  
CSA Standard: C22.2 No. 42  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: Yes  
UL Standard: UL498  
UN SPSC: 39121406  
UR: No

#### DIMENSIONS

Depth (US): 1.878"  
Height (US): 4.478"  
Width (US): 2.74"

#### TECHNICAL INFORMATION

Amps: 15A  
NEMA Configuration Number: 5-15R  
Volts: 125V  
Volts (AC): 125  
Grade Type: Specification

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

