



POWER OUTLET RECEPTACLE OPENINGS, TWO GANG, CHROME

S3862C | [Pass & Seymour](#)

FEATURES & BENEFITS

Two Gang Power Outlet Receptacle Opening, 2.1563" hole for 2.125" diameter device - 4 mtg. holes, Smooth Metal.

- Chrome: .040" thick.
- 70% copper, 30% zinc alloy gives warm, appealing finish to modern decor as well as retrofit applications.
- Lacquered to prevent corrosion.
- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

SPECIFICATIONS

GENERAL INFO

Size: Standard

Type: Single

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: Yes

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: Yes

UN SPSC: 39121704

UR: No

DIMENSIONS

Diameter (US): 2.1563"

TECHNICAL INFORMATION

Material: Chrome
Capacity: 2-gang

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant





POWER OUTLET RECEPTACLE OPENINGS, TWO GANG, CHROME

S3862C | [Pass & Seymour](#)

FEATURES & BENEFITS

Two Gang Power Outlet Receptacle Opening, 2.1563" hole for 2.125" diameter device - 4 mtg. holes, Smooth Metal.

- Chrome: .040" thick.
- 70% copper, 30% zinc alloy gives warm, appealing finish to modern decor as well as retrofit applications.
- Lacquered to prevent corrosion.
- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

SPECIFICATIONS

GENERAL INFO

Size: Standard

Type: Single

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: Yes

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: Yes

UN SPSC: 39121704

UR: No

DIMENSIONS

Diameter (US): 2.1563"

TECHNICAL INFORMATION

Material: Chrome
Capacity: 2-gang

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

