



S3912

15T6/145V
15 watt T6 Incandescent; Clear; 2000 average rated hours; 90 lumens; Candelabra base; 145 volts

Features

- Special application incandescent
- 145 volt



S3912

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | Voltage |
|-------------|--------------|-------|------------|------------|-----------|-----------|---------|
| S3912 | 045923039126 | 15 | T6 | Candelabra | E12 | 15T6/145V | 145 |

| Finish | MOL In Inches | MOD In Inches | Filament | Initial Lumens | Average Rated Hours | Pack | Package Type |
|--------|---------------|---------------|----------|----------------|---------------------|------|--------------|
| Clear | 3 1/16" | 0.75" | C-5A | 90 | 2000 | 120 | Sleeve/10 |

| RoHS Compliant |
|----------------|
| Yes |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

