



S3929

100A/RS/TF/2PK

100 watt A19 Incandescent; Frost; 5000 average rated hours;
960 lumens; Medium base; 130 volts; Shatter Proof; 2/Pack

Features

- Shatterproof coated incandescent
- Vibration service
- Long life
- Brass Base
- 130 volt




S3929

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3929	045923039294	100	A19	Medium	E26	100A/RS/TF/2PK	130

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Frost Shatter Proof	4 1/8"	2.38"	C-9	960	5000	24	2pk

RoHS Compliant							
Yes							



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S3929

100A/RS/TF/2PK

100 watt A19 Incandescent; Frost; 5000 average rated hours;
960 lumens; Medium base; 130 volts; Shatter Proof; 2/Pack

Features

- Shatterproof coated incandescent
- Vibration service
- Long life
- Brass Base
- 130 volt



S3929

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3929	045923039294	100	A19	Medium	E26	100A/RS/TF/2PK	130

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Frost Shatter Proof	4 1/8"	2.38"	C-9	960	5000	24	2pk

RoHS Compliant							
Yes							



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

