



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S39394 54W Led/Hid 50K 100-277VP *Satco*

Catalog Number	S39394
Manufacturer	Satco
Description	Satco S39394 54W/Led/Hid/5000K/100-
Weight per unit	2.4 (lbs/each)
Product Category	Led Specialty Lamps & Modules

Features

average life	50000
Base	Mogul Extended
beam angle	300
dimmable	No
lumens	7722
Material	Plastic; Aluminum
Shape	Corncob
surge protection	Built-in surge protection - 4KV
Voltage Rating	277
Warranty	5 Year Limited - Hi-Pro
Wattage	54

Material, Color, and Finish

color temperature	5000
-------------------	------

Dimensions and Weight

Diameter	3.34
Length	9.03

Descriptions

Description	54W LED/HID 50K 100-277VP
Long Description	SATCO S39394 54W/LED/HID/5000K/100-
Product Type	54W/Led/Hid/5000K/100-277V/Ex39
Special Features	Warranty: 5 Year Limited ; Country of origin: China ; IP65 rated: Yes ; CEC: Lawful for sale in California ; Operating Temp: -20C (-4F) to a maximum of +40C (+104F) ; Safety Listing: cULus - Wet ; Beam spread: 300 degrees ; Burning position: Universal ; Color temp: Natural Light ; Incandescent equivalent: 300W ; Fluorescent equivalent: 85W ; HID equivalent: 250W ; Voltage:100-277V



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Satco
GTIN	00045923303944
Manufacturers Part Number	S39394
sub brand	Satco
UPC	045923303944

Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
Type	HID Replacements

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Weight	1.89
Weight Per each	2.35

Uses, Certifications, and Standards

Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)
-----------------------	--