



# S3970

75A/RS

75 watt A19 Incandescent; Frost; 2500 average rated hours; 710 lumens; Medium base; 130 volts; 2/Pack

### Features

- General Service Incandescent
- Household or Commercial use
- Long Life
- Rough Service
- 130 volt



S3970

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S3970	045923039706	75	A19	Medium	E26	75A/RS	130

Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours	Pack	Package Type
Frost	4 1/8"	2.38"	C11/5	710	2500	24	2pk

RoHS Compliant
Yes



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

