



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S39751 40W Led Hid RPL (Adj LT PNLS)

Satco

Catalog Number	S39751
Manufacturer	Satco
Description	40 Watt Led Hid Replacement - 5000K - Mogul Extended Base - Adjustable Beam Angle - 100-277 Volts
Weight per unit	2.2 (lbs/each)
Product Category	Lighting

### Features

average life	50000
Base	EX39
beam angle	120/150/260
dimnable	Non-Dimmable
lumens	5600
Material	Thermo Plastic (PBT); Steel; Aluminum
Power Factor	>0.9
Shape	ED28
surge protection	Built-in surge protection - 4KV
voltage range	277
Voltage Rating	120 to 277
Warranty	5 Year Limited - Hi-Pro
Wattage	40

### Material, Color, and Finish

color rendering index (cri)	80+
color temperature	5000
Finish	Clear

### Dimensions and Weight

Size	7.24
------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	40W LED HID RPL (ADJ LT PNLS)
extra long description	SATCO S39751 40W/LED/HID/MB-G3/50K/
Long Description	40 Watt LED HID Replacement - 5000K - Mogul Extended Base - Adjustable Beam Angle - 100-277 Volts
Product Type	40W/Led/Hid/MB-G3/50K/100-277V
Special Features	Warranty: 5-Years ; Location Rating: Damp ; Operating Temp: -20C (-4F) to +65C (+149F) ; Material: Aluminum / Steel / Thermo Plastic (PBT) ; Indoor Outdoor: Indoor;Outdoor ; Surge Protection: Built-in surge protection - 4KV ; Color Temp: Natural Light ; Efficacy: 140.00 LPW ; DLC Approved: False ; FCC Compliant: True ; Indoor Outdoor: Indoor;Outdoor ; Lamp Filament: LED ; ANSI Base: EX39 ; Lamp Ballast Type AB: Type B ; Amps: 0.400-0.144A ; T24 Compliant: False

## Manufacturer Information

Brand	Satco
GTIN	00045923397516
Manufacturers Part Number	S39751
UPC	045923397516

## Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
Type	LED HID Replacements

## Packaging

Carton	6
Package	12
Weight	1.85
Weight Per each	2.17

## Uses, Certifications, and Standards

Application	LED
Operating Temperature standard	-20C (-4F) to a maximum of +65C (+149F) cULus - Certified;cULus - Classified;cULus - Listed