SATCO NUVO

Project Name

Location

Prepared By



SATCO S39751

40W/LED/HID/MB-G3/50K/100-277V

Notes

[www] 11-22-2021 02:57:4

General	
Status	Active
Watts	40W
Incandescent Equivalent	300W
Fluorescent Equivalent	65W
HID Equivalent	175W
Volts	100V-277V
Shape	Corncob
Base	Mogul Extended
ANSI Base	EX39
Finish	Clear
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	80
Lumens	5600L
Beam Spread	120;150;260
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	LED HID
Technology	LED
	Width: 8.00 in. Depth: 8.00 in.
Min Compartment Size	Height: 11.00 in.
Electrical	
Operating Frequency	50/60 Hz
Power Factor	>0.9
Surge Protection	Built-in surge protection - 4KV
THD	<20%
Operating Temperature	-20C (-4F) to a maximum of +65C (+149F)
Physical	
MOL	7.24
MOD	3.35
Lens Finish	Clear
Lens Material	Thermo Plastic (PBT)
Housing Color	White
Photocell	Optional Add-On
Weight (lb.)	1.85
Additional Information	
Additional Info	PIR Sensor available as an accessory
Rated For Enclosed Fixture	Yes
IP Rating	IP64
Specification Note	Closed 260 deg; Partial 150 deg; Open 120 deg
Warranty	5 Year Limited - Hi-Pro
Compliance	
Safety Listing	cULus Classified
Location Rating	Damp
Energy Star	No
DLC Approved	Yes

DLC ID	PLISIESIO4OC
California Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

Copyright 2020 Satco Products, Inc. All Rights Reserved

For More Information Visit: http://www.satco.com/







