



S4129

50MR16/GU10 /FL /FR
50 watt; Halogen; MR16; Frosted; 2000 Average rated Hours;
520 Lumens; GU10 base; 120 volts

Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output



S4129

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S4129	045923041297	50	MR16	GU10	GU10	50MR16/GU10 /FL /FR	120
MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color	Average Rated Hours	Pack
1 7/8"	2.00"	CC-8	520	2900	Warm White	2000	240/12
Package Type		Beam Spread		Lens	CBCP	RoHS Compliant	
Box		FL 36		Y	900	Yes	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

