



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S4881 40W A15 Tough Coat 265LM

Satco

Catalog Number	S4881
Manufacturer	Satco
Description	Incandescent Shatter Proof Lamp, A15 Shape, 265 LM Brightness (Lumens), 40 W, 130 V, Frosted, Brass Base Material, C-9 Filament, 2500 H Average Life, E26 Medium Base, Dimmable, 1.88 In Diameter, 3-1/2 In Height, 0.09 LB
Weight per unit	0.0935 (lbs/each)
Product Category	Shatter Resistant Incandescent

Features

Base	Medium
lumens	265
Voltage Rating	130
Warranty	Avg. Rated Hour Limited

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Diameter	1.88
Length	3.5

Descriptions

Description	40W A15 TOUGH COAT 265LM
extra long description	SATCO S4881 40A15/TF SHATTER PROOF
Special Features	Shatter-proof

Manufacturer Information

GTIN	00045923048814
UPC	045923048814

Taxonomies, Classifications, and Categories

Category Description	INCANDESCENT
Type	Shatter Proof

Packaging

Carton	25
Weight Per each	0.0935

Uses, Certifications, and Standards

standard	RoHS Compliant
----------	----------------