



# S4885

250R40/1/TF  
250 watt R40 Incandescent; Clear Heat; 6000 average rated hours; Medium base; 120 volts; Shatter Proof

### Features

- Shatterproof coated incandescent
- Vibration service
- Long life
- Brass base
- Approved for use in food warming fixtures



S4885

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S4885	045923048852	250	R40	Medium	E26	250R40/1/TF	120

Finish	MOL In Inches	MOD In Inches	Filament	Average Rated Hours	Pack	Package Type	RoHS Compliant
Clear Heat Shatter Proof	6 7/8"	5.00"	C-9	6000	12	Sleeve	Yes



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

