



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1915 Turning Basin Suite 500
77029-0000, TX Houston
Phone: 713-675-6700
Fax: 713-675-6777



S49392 36W Led Hid RPLC 50K Med Base 4968LM

Satco

Catalog Number	S49392
Manufacturer	Satco
Description	36 Watt Led Hid Replacement - 80 Cri - 5000K - Medium Base - Economy Hi-Pro
Weight per unit	1.6 (lbs/each)
Product Category	Lighting

Features

average life	35000
Base	E26
beam angle	300
dimmable	Non-Dimmable
lumens	4968
Power Factor	>0.9
Shape	Corn-cob
Voltage Rating	120 to 277
Wattage	36

Material, Color, and Finish

color rendering index (cri)	80+
color temperature	5000
Finish	white

Dimensions and Weight

Size	7.16
------	------

Descriptions

Description	36W LED HID RPLC 50K MED BASE 4968LM
extra long description	SATCO S49392 36W/LED/HP/850/100-277
Long Description	36 Watt LED HID Replacement - 80 CRI - 5000K - Medium Base - Economy Hi-Pro
Product Type	36W/Led/HP/850/100-277V/E26
Special Features	Warranty: 5-Years ; Location Rating: Damp ; Operating Temp: -30C (-22F) to +50C (+122F) ; Material: Aluminum / Polycarbonate (PC) ; Indoor Outdoor: Indoor;Outdoor ; Surge Protection: Built-in surge protection - 3KV ; Color Temp: Natural Light ; Efficacy: 138.00 LPW ; DLC Approved: False ; FCC Compliant: True ; Indoor Outdoor: Indoor;Outdoor ; Lamp Filament: LED ; ANSI Base: E26 ; Lamp Ballast Type AB: Type B ; Amps: 0.360-0.130A ; T24 Compliant: False



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1915 Turning Basin Suite 500
77029-0000, TX Houston
Phone: 713-675-6700
Fax: 713-675-6777

Manufacturer Information

Brand	Satco
GTIN	00045923493928
Manufacturers Part Number	S49392
UPC	045923493928

Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
Type	LED HID Replacements

Packaging

Carton	1
Weight Per each	1.57

Uses, Certifications, and Standards

Application	LED
standard	cULus - Certified;cULus - Classified;cULus - Listed