SATCO NUVO

Project Name



Prepared By

SATCO S49394

54W/LED/HP/850/100-277V/EX39

Notes

General	
Status	Active
Watts	54W
HID Equivalent	250W
Volts	100V-277V
Shape	Corncob
Base	Extended Mogul
ANSI Base	EX39
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	80 7452L
Lumens	300
Beam Spread	
Dimmable Hours Rated	Non-Dimmable
	35000 LED HID
Lamp Type	
Technology	LED
Min Compartment Size	Length: 8 in. Width: 8 in. Height: 15.75 in.
Ballasting Requirements	Ballast Bypass
Electrical	
Operating Frequency	50/60 Hz
Power Factor	>0.9
Burning Position	Base Up, Base Down, or Horizontal
Surge Protection	Built-in surge protection - 3KV
Operating Temperature	-30C (-22F) to a maximum of +65C (+149F)
Physical	
MOL	8.78
MOD	3.35
Lens Finish	Clear
Lens Material	Polycarbonate (PC)
Housing Color	White
Photocell	No
Weight (lb.)	1.90
Additional Information	
Rated For Enclosed Fixture	Yes
IP Rating	IP65
Warranty	3 Year Limited
Compliance	
Safety Listing	cULus Classified; cULus Listed
Location Rating	Damp
Energy Star	No
RoHS Compliant	Yes
FCC Compliant	Yes
·	
SDS Sheet	LED_Lamp









All nights neserved http://www.satco.com/
