S4999

250R40/1
250 watt R40 Incandescent; Clear Heat; 6000 average rated hours; Medium base; 120 volts

Features
- General Service Reflector
- Household or Commercial use
- Long Life
- Brass Base

S4999

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S4999	045923049996	250	R40	Medium	E26	250R40/1	120

Finish	MOL In Inches	MOD In Inches	Filament	Average Rated Hours	Pack	Package Type	RoHS Compliant
Clear Heat	6 1/2"	5.00"	C-9	6000	12	Sleeve	Yes

National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051

S4999

250R40/1
250 watt R40 Incandescent; Clear Heat; 6000 average rated hours; Medium base; 120 volts

Features
- General Service Reflector
- Household or Commercial use
- Long Life
- Brass Base

S4999

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S4999	045923049996	250	R40	Medium	E26	250R40/1	120

Finish	MOL In Inches	MOD In Inches	Filament	Average Rated Hours	Pack	Package Type	RoHS Compliant
Clear Heat	6 1/2"	5.00"	C-9	6000	12	Sleeve	Yes

National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051