



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **S5831 250W Probe Start Metal Halide 4K Mog Base Ed28**

Satco

|                  |                                                                                                                                                                                                                                                     |
|------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | S5831                                                                                                                                                                                                                                               |
| Manufacturer     | Satco                                                                                                                                                                                                                                               |
| Description      | Hid Metal Halide Lamp, Designation: MH250/ED28/U/4K, 250 WTT, ED28 Shape, E39 Mogul Base, Clear, 12000 HR, Lumens: 20000 LM Initial, 4000 Deg K Color Temperature, Cool White 65 Cri, 8-5/16 In Length, 3-1/2 In Diameter, Burn Position: Universal |
| Weight per unit  | 0.7500 (lbs/each)                                                                                                                                                                                                                                   |
| Product Category | Hid Quartz Metal Halide Lamps                                                                                                                                                                                                                       |

### **Features**

|                    |                         |
|--------------------|-------------------------|
| average life       | 12000                   |
| Base               | Mogul                   |
| lumens             | 20k                     |
| Operating Position | Universal               |
| Shape              | ED28                    |
| start type         | Probe Start             |
| Warranty           | Avg. Rated Hour Limited |
| Wattage            | 250                     |

### **Material, Color, and Finish**

|                             |       |
|-----------------------------|-------|
| Color                       | White |
| color rendering index (cri) | 65    |
| color temperature           | 4000  |
| Finish                      | Clear |

### **Dimensions and Weight**

|          |      |
|----------|------|
| Diameter | 3.50 |
| Length   | 8.31 |

### **Descriptions**

|                        |                                                                                                                                                                                                                                                     |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | 250W PROBE START METAL HALIDE 4K MOG BASE ED28                                                                                                                                                                                                      |
| extra long description | SATCO S5831 MH250/U MOG                                                                                                                                                                                                                             |
| Long Description       | HID Metal Halide Lamp, Designation: MH250/ED28/U/4K, 250 WTT, ED28 Shape, E39 Mogul Base, Clear, 12000 HR, Lumens: 20000 LM Initial, 4000 DEG K Color Temperature, Cool White 65 CRI, 8-5/16 IN Length, 3-1/2 IN Diameter, Burn Position: Universal |
| Product Type           | MH250/U Mog                                                                                                                                                                                                                                         |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Satco          |
| GTIN                      | 00045923058318 |
| Manufacturers Part Number | S5831          |
| UPC                       | 045923058318   |

## Taxonomies, Classifications, and Categories

|                      |              |
|----------------------|--------------|
| Category Description | METAL HALIDE |
| Type                 | METAL HALIDE |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 12   |
| Weight Per each | 0.75 |

## Uses, Certifications, and Standards

|          |                |
|----------|----------------|
| standard | RoHS Compliant |
|----------|----------------|